

Maxima™ Advanced Ultrasonic Cleaner MA100

Dual-Frequency
Cleaning in
a Compact,
User-Friendly
Design.

Experience powerful performance, high-speed cleaning, and versatile functionality—all in a compact 1.06-gallon design. Choose 32kHz for a fast, intense surface cleaning, or 48kHz for a deeper, more precise and gentler clean.



DUAL
FREQUENCY



INDUSTRY-LEADING
FAST CYCLE
CLEAN TIME



QUIET
OPERATION-
<80DBA



3-YEAR
WARRANTY

maxima®

by HENRY SCHEIN®

Performance Handpieces & Small Equipment

Explore the New Maxima: HenryScheinDental.com/Maxima

Maxima[™] Advanced Ultrasonic Cleaner MA100

Highlights

- **Dual-frequency ultrasonic cleaning:**
32 kHz delivers powerful surface cleaning.
48 kHz provides precise, gentle crevice cleaning and operates at a quieter frequency
- **Compact size** with a 1.06-gallon tank fits two half-size cassettes (8" x 5.5")
- **Powerful cleaning** with transducer technology
- **Quiet operation** at less than 80 dBA
- **Industry-leading fast cycle** time in as little as 5 minutes*
- Backed by **3-year warranty**

*5 minutes per layer of instruments

Features

- Simple rotary knob with digital LED display
- 2-minute auto degas boosts cleaning performance
- Moisture-resistant circuit boards
- Dual cooling fans for longer lifespan
- Rear drainage port for easy setup
- Built-in overheating protection (30-min limit + cooldown)
- Memory function for timer/frequency recall
- Durable aluminum-wrapped housing

Ultrasonic Frequency	Low 32 KHz High 48 KHz
Net Weight	15.9lb
Unit Size	15.6"L x 11.7"W x 9.3"H

Tank Capacity	1.06 gallon (US) / 4.0 L (Min 1.8 L / 0.5 gal, Max 3.65 L / 1.0 gal)
Tank Size	9.8"L x 6.9"W x 4.1"H
Longest Item Fits Inside Tank	10.4" L
Timer Settings	5 min 7.5 min 10 min 12.5 min 15 min



Maxima[™] Advanced Ultrasonic Cleaner MA100

INCLUDED IN BOX: Ultrasonic Cleaning Unit | Stainless Steel Basket | Drain Hose (39" Long) | Drainer Strainer | Power Cord | Instructions for Use

(570-4851)

OTHER ACCESSORIES

Maxima Advanced MA100 Cleaning Chamber (570-5407)

Maxima Advanced MA100 Beakers (570-5406)

(Includes: 2 Beakers and 1 Holder)

Explore the New Maxima:
HenryScheinDental.com/Maxima

